

PRODUCT DATASHEET

SP HOLDER DN68 H65

SPOT HOLDER | Spacer to increase distance between spotlight and thermal insulation material



Areas of application

- Ceilings in low energy houses
- Ceilings with thermal insulation material

Product benefits

- Increase distance between spotlight and thermal insulation material
- Protects moisture barrier foil from hot surface of spotlight and driver
- Robust: 4-leg spacer to hold thermal insulation material
- Improved lifetime for LED and driver thanks to increased air-volume

Product features


- Material: fibre-reinforced polyamide PA66
- Glow Wire Test according to IEC 60695-2-12: 850 °C
- Suitable only for LEDVANCE SPOTs in 68 mm cut-out



TECHNICAL DATA

Dimensions & Weight

Length	93.0 mm
Width	93,0 mm
Height	73 mm
Product weight	19.00 g



Materials & Colors

Product color	Grey
Body material	Polyamid (PA)

Application & Mounting

Ambient temperature range	-20...+40 °C
Mounting type	Recessed
Mounting location	Ceiling
Mounting diameter	68...83 mm
Mounting depth	65,0 mm

Certificates & Standards

Standards	CE / CB / UKCA / EAC
-----------	----------------------

Safety advice

- This spacer is only allowed to be used in combination with SP AIR FIX or SP AIR ADJ!

DOWNLOAD DATA

Documents and certificates	
	User instruction

Documents and certificates	
	Declarations Of Conformity CE
Tender texts	
	Tender documents

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4099854013478	BAG 1	95 mm x 95 mm x 73 mm	23.00 g	0.66 dm ³
4099854013485	Shipping box 20	175 mm x 175 mm x 135 mm	522.00 g	4.13 dm ³
4099854013492	Shipping box 360	550 mm x 545 mm x 300 mm	2291.00 g	89.93 dm ³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.