


disabled persons call system

The Wandsworth Disabled Person's Call System, for use in toilets and bathrooms fully complies with the guidelines outlined in BS8300:2009 + A1:2010 it quickly enables location of any person who is in difficulty.

The simple to install system is available as a complete 'boxed' kit for ease of specification and ordering. Alternatively components can be ordered to suit a customer specification or large system requirement. Plates are finished in stainless steel as standard. Multiple Toilet call points can be connected to a multi display panel located in a centrally staffed area.



QD342



Remote Indicator Panels

Remote indicator panels for multiple disabled person's call systems. These panels would normally be located in a centrally staffed area (e.g. reception or security office) of the building and all toilet/bathroom calls would be routed back for indication of alarm calls.

There are four standard indicator panels, each with 1.1 Watt amber indicator lamps, one mini bleep tone buzzer and rocker switch for muting buzzer, Standard Engraving: MUTE BUZZER.

QD340

3 indicator lamps
front cover plate measuring 172mm square.

QD341

6 indicator lamps
front cover plate measuring 172mm square.

QD342

12 indicator lamps
front cover plate measuring 248mm x 172mm

QD343

18 indicator lamps
front cover plate measuring 248mm square.

For further information on multiple systems, please contact the Wandsworth technical services department.

within the toilet cubicle

QD322/QD351



Ceiling Pull

A white surface mounted ceiling pull unit, with a 3 meter amber cord. The unit contains an integral reassurance light 2.5 watt with amber lens. Unit is supplied with 2 amber ring pull units (QD351) or 1 amber acorn pull unit (QD322). Unit fits BS31 box with 50.38mm centres.

* note QD351 supplied in QD350 for BS compliance.

QD321



Call Unit

An extra/alternative unit to the QD322/QD351, the unit consists of a front cover plate measuring 86mm square and containing an orange call button marked with a nurse call symbol. There is a red LED reassurance light above the button.

Box flush: 1702/G Box
Box surface: 1132/W

QD324



Reset Unit

Used in conjunction with a call unit (QD321) or ceiling pull (QD322/QD351). The QD324 unit is also supplied as part of the QD350 complete system. Front cover plate measuring 146mm x 86mm containing: Reset push with integral reassurance light 1.1 watt with amber lens. PCB components wired to terminal block.

Box flush: 1703/G Box
Box surface: 1133/W

outside toilet facility

QD331



Single Overdoor Lamp

Usually mounted above the toilet door, this unit comprises a front cover plate 86mm square containing: One 2.8watt MES lamp. (Lenses QD337, are to be ordered separately; see below for details). Component wired to terminal block.

Box flush: 1702/G
Box surface: 1132/W

QD332



Overdoor Lamp/ Tone Generator

Providing both an audible and visual call signal, the QD322 unit is also supplied as part of the QD350 complete system. The front cover plate measures 146mm x 86mm and contains: One 2.8watt MES lamp. (Lenses QD337, are to be ordered separately; see below for details). One mini bleeptone generator. Component wired to terminal block.

Box flush: 8302/G
Box surface: 8387/W

QD337

Overdoor Lamp Lens

Lamp lenses, 36mm square, are available in amber (A), red (R), green (G), blue (BL), or clear (CL). Please specify colours and quantities of each required.

QD153

Power Unit

Input 230V 50 Hz, an earth connection is required. Rated output 1A 24Vdc. Output fuse 1A quickblow 20mm x 5mm.

Size: L 200mm x W 100mm x H 100mm
Power Unit Weight: 1.5 KG.

QD350

Complete System

The QD350 complete system (Flush Mounting) comprises the following components:

- 1 x QD351 Ceiling Pull
- 1 x QD324 Reset Unit+ Flush box 1703/G
- 1 x QD332 Overdoor lamp/tone generator+ Flush box 8302/G
- 1 x QD337/A lens
- 1 x QD153 Power supply unit

assured.
practical

For more information
Tel: 01483 713400
Email: info@wandsworthgroup.com
www.wandsworthgroup.com