

Floor Standing Enclosures
Steel Range

Accessories | Mounting plates

Mounting plates, MP

Description:	Standard mounting plate. It can also be mounted on the side of an enclosure by using MPS kit or slid in from the side with the MTS profile. For heavy loads in vibrating environments use mounting plate reinforcement profile MPR and MPE or MPEF brackets.
Material:	3 mm galvanized steel.
Pack quantity:	1 piece.
Maximum load:	6000 N.
Mounting requirements:	Use MPA for mounting the MP inside the enclosure. Adjustable in depth with MPD accessory.

For enclosure		Mounting plate dimensions		Item no.
H	W	h	w	
1200	600	1094	494	MP1206
1200	800	1094	694	MP1208
1200	1200	1094	1094	MP1212
1400	600	1294	494	MP1406
1400	800	1294	694	MP1408
1400	1000	1294	894	MP1410
1400	1200	1294	1094	MP1412
1600	600	1494	494	MP1606
1600	800	1494	694	MP1608
1600	1000	1494	894	MP1610
1600	1200	1494	1094	MP1612
1800	400	1694	294	MP1804
1800	500	1694	394	MP1805
1800	600	1694	494	MP1806
1800	800	1694	694	MP1808
1800	1000	1694	894	MP1810
1800	1200	1694	1094	MP1812
1800	1600	1694	1494	MP1816
2000	400	1894	294	MP2004
2000	500	1894	394	MP2005
2000	600	1894	494	MP2006
2000	800	1894	694	MP2008
2000	1000	1894	894	MP2010
2000	1200	1894	1094	MP2012
2000	1600	1894	1494	MP2016
2200	600	2094	494	MP2206
2200	800	2094	694	MP2208
2200	1000	2094	894	MP2210
2200	1200	2094	1094	MP2212

500 mm width mounting plates for side mounting available on request.
1600 mm wide mounting plates are supplied as two 800 mm wide mounting plates along with a MPF filler plate.



Mounting plate brackets, MPA

Description:	To fix mounting plates in the enclosure, including brackets for depth adjustment in steps of 25 mm. Brackets are needed when an extra mounting plate is required or when the enclosure is ordered without mounting plate (PE).
Material:	3 mm zinc plated steel.
Pack quantity:	2 top brackets, 2 bottom sliding brackets and 2 adjustment brackets with mounting accessories.


Item no.
MPA06



Mounting plate adjustment brackets, MPD

Description:	Brackets to adjust the mounting plate in depth by steps of 25 mm in the enclosure frame.
Material:	3 mm zinc plated steel.
Pack quantity:	2 brackets with mounting accessories.

Item no.
MPD02



Mounting brackets rear fixing, MPA

Description:	To fix mounting plates in the enclosure. Brackets are needed when an extra mounting plate is required or when the enclosure is ordered without mounting plate (PE).
Material:	3 mm zinc plated steel.
Pack quantity:	2 top brackets and 2 bottom sliding brackets with mounting accessories.

Item no.
MPA04

