

technical hotline +44 (0)1268 563720

decorative | wiring devices

Key Operated Socket Outlet and Switch

2 GANG
UNSWITCHED
SOCKET
FLUSH

13 AMP 1 GANG DP
DUAL EARTH KEY
OPERATED SOCKET
FLUSH

20 AMP 1 GANG DP
KEY OPERATED
SWITCH
FLUSH

Floor Mounted Socket Outlets 13 AMP

1 GANG
SWITCHSOCKET
SPRING LOADED
HINGED COVER
PLATE

1 GANG
SWITCHSOCKET
SPRING LOADED
HINGED COVER
PLATE

2 GANG SOCKET
WITH SPRING
LOADED
HINGED COVER
PLATE



K733CEBLU 5
"CLEAN EARTH" FACILITY.
ENGRAVED "MEDICAL
EQUIPMENT ONLY"

K2949BSS 5

K2158BSS 5

740BSS 10

741BSS 10

742BSS 5

740BRC 10

741BRC 10

742BRC 5

740SAG 10

741SAG 10

742SAG 5

K2947CEBLU
K733CEBLU
These product are provided
with facilities for "clean
earth" connection.
BS 1363 Pt 2: 1995
Product complies with the
Medical Electrical Installation
Guidance Notes (MEIGaN)

MOUNTING BOXES:
FLUSH 35mm:
1 GANG: 866ZIC
2 GANG: 886ZIC
SURFACE WITH KNOCKOUTS:
1 GANG: K899ALM
2 GANG: K897ALM
WITHOUT KNOCKOUTS:
1 GANG: K829ALM
2 GANG: K830ALM
DIMENSIONS:
1 GANG: 86 x 86mm
2 GANG: 86 x 146mm
K2949
BS 1363: Pt2: 1995

MOUNTING BOXES:
FLUSH 35mm:
1 GANG: 866ZIC
2 GANG: 886ZIC
SURFACE WITH KNOCKOUTS:
1 GANG: K899ALM
2 GANG: K897ALM
WITHOUT KNOCKOUTS:
1 GANG: K829ALM
2 GANG: K830ALM
DIMENSIONS:
1 GANG: 86 x 86mm
2 GANG: 86 x 146mm
K2158
BS EN 60669 – 1: 1999

MOUNTING BOXES:
FLUSH:
1 GANG: 866ZIC
2 GANG: 886ZIC
Boxes must have a minimum
depth of 35mm
Rotary operated shutter.
DIMENSIONS:
1 GANG: 102 x 86mm
2 GANG: 102 x 146mm
FIXING CENTRES:
1 GANG: 60.3mm
2 GANG: 120.6mm
BS 1363 Pt2: 1995

MOUNTING BOXES:
FLUSH:
1 GANG: 866ZIC
2 GANG: 886ZIC
Boxes must have a minimum
depth of 35mm
Rotary operated shutter.
DIMENSIONS:
1 GANG: 102 x 86mm
2 GANG: 102 x 146mm
FIXING CENTRES:
1 GANG: 60.3mm
2 GANG: 120.6mm
BS 1363 Pt2: 1995

MOUNTING BOXES:
FLUSH:
1 GANG: 866ZIC
2 GANG: 886ZIC
Boxes must have a minimum
depth of 35mm
Rotary operated shutter.
DIMENSIONS:
1 GANG: 102 x 86mm
2 GANG: 102 x 146mm
FIXING CENTRES:
1 GANG: 60.3mm
2 GANG: 120.6mm
BS 1363 Pt2: 1995