

Switchsocket Outlets RCD Protected

1 GANG

30MA RATED
TRIPPING CURRENT
PASSIVE CONTROL
CIRCUIT **FLUSH**

Socket Outlets 13 AMP

2 GANG WITH
DUAL EARTH
TERMINALS
FLUSH

MEIGaN Socket Outlets

13 AMP

1 GANG DP
SWITCHED
FLUSH1 GANG DP
UNSWITCHED
FLUSH2 GANG DP
WITH OUTBOARD
ROCKERS
FLUSH

FINISHES

BRUSHED STAINLESS STEEL	K6304BSS	5	K733BSS	5	K2958BLU 1 ENGRAVED "MEDICAL EQUIPMENT ONLY"	K732BLU 1 ENGRAVED "MEDICAL EQUIPMENT ONLY"	K2947CEBLU 5 "CLEAN EARTH" FACILITY. ENGRAVED "MEDICAL EQUIPMENT ONLY"
BRUSHED CHROME			K733BRC	5			
SATIN GOLD							
POLISHED CHROME			K733PCR	5			

It is important to ensure that the correct control circuit, active or passive, is selected for each application.

Only suitable for supply voltage of 240V a.c., 50Hz.
BS 7288: 1990

High Integrity Earthing

K733 is fitted with two earth terminals to provide a double earth facility when installations require a high integrity protective connection as specified within BS 7671 IEE Wiring Regulations.

Product complies with the Medical Electrical Installation Guidance Notes (MEIGaN)

Product complies with the Medical Electrical Installation Guidance Notes (MEIGaN)

K2947CEBLU K733CEBLU

These product are provided with facilities for "clean earth" connection.

Product complies with the Medical Electrical Installation Guidance Notes (MEIGaN)

MOUNTING BOXES:

FLUSH 25mm

1 GANG: 861ZIC

2 GANG: 862ZIC

FLUSH 35mm (for extra wiring space)

1 GANG: 866ZIC

2 GANG: 886ZIC

SURFACE WITH KNOCKOUTS:

1 GANG: K899ALM

2 GANG: K897ALM

WITHOUT KNOCKOUTS:

1 GANG: K829ALM

2 GANG: K830ALM

DIMENSIONS:

1 GANG: 86 x 86mm

2 GANG: 86 x 146mm

FIXING CENTRES:

1 GANG: 60.3mm

2 GANG: 120.6mm

BS 1363 Pt 2: 1995

(except for K6304)